



## PANGO CLAW® (3" WIDE)


A STEGO TECHNOLOGY, LLC INNOVATION | VAPOR BARRIER 31 31 16, 07 26 00, 03 30 00 | VER: 10/19/2017

### 1. PRODUCT NAME

**PANGO CLAW (3" WIDE)**

### 2. MANUFACTURER

C/O Stego Industries, LLC\*  
216 Avenida Fabricante, Suite 101  
San Clemente, CA 92672  
Sales, Technical Assistance  
Ph: (877) 464-7834  
Fx: (949) 257-4113  
www.stegoindustries.com



### 3. PRODUCT DESCRIPTION

**USES:** Pango Claw is a multi-layered tape that is used to seal Pango® Wrap along its terminating edges (interior and perimeter) to the slab while the concrete is placed. Pango Claw allows wet concrete to cast into the textured top surface to form a mechanical bond/seal.

**COMPOSITION:** Pango Claw is composed of polyethylene film, aperture film, and an acrylic, pressure-sensitive adhesive.

**SIZE:** Pango Claw (3" Wide) is 3" X 180'. Pango Claw (3" Wide) ships 16 rolls in a case.

### 4. TECHNICAL DATA

**TABLE 1: PHYSICAL PROPERTIES OF PANGO CLAW (3" WIDE)**

PROPERTY	TEST METHOD	RESULTS
Total Thickness		26 mil
Permeance	ASTM F1249 – Test Method for Water Vapor Transmission Rate Through Plastic Film and Sheeting Using a Modulated Infrared Sensor	0.074 perms
180° Adhesion Peel Strength	ASTM D903	10.0 lbf/in.
Shear Adhesion Strength	1 in <sup>2</sup> shear test using an Instron 3345 Machine	31 lbf/in <sup>2</sup> **
Dimensions		3" x 180'

Note: perm unit = grains/(ft<sup>2</sup>\*hr\*in-Hg)

### 5. INSTALLATION

**UNDER SLAB:** Clean surface of Pango Wrap to ensure that it is free of moisture, frost, dirt, and debris prior to the installation of Pango Claw. When ready to apply Pango Claw, peel back the release liner and apply to Pango Wrap. Pango Claw should be completely on Pango Wrap.

To detail, cut Pango Claw with a box knife or scissors. Pango Claw should be installed above 40°F for maximum adhesion. For additional information please refer to Pango's complete installation instructions.

**TIP:** Wrap the release liner back over the entire roll while unrolling Pango Claw. This technique will allow the release liner to pull off easily and keep it out of the way.

Review Pango Wrap's complete installation instructions prior to installation.

*Continued...*

Note – legal notice on page 2.

## PANGO CLAW® (3" WIDE)

A STEGO TECHNOLOGY, LLC INNOVATION | VAPOR BARRIER 31 31 16, 07 26 00, 03 30 00 | VER: 10/19/2017

### 6. Availability & Cost

Pango Claw (3" Wide) is available through our network of building supply distributors. For current cost information, contact your local Pango distributor or Stego Industries' Sales Representative.

### 7. WARRANTY

Stego Industries, LLC believes to the best of its knowledge, that specifications and recommendations herein are accurate and reliable. However, since site conditions are not within its control, Stego Industries does not guarantee results from the use of the information provided and disclaims all liability from any loss or damage. Stego Technology, LLC does offer a limited warranty on Pango Wrap. Please see [www.stegoindustries.com/legal](http://www.stegoindustries.com/legal).

### 8. MAINTENANCE

Store Pango Claw in a dry and temperate area.

### 9. TECHNICAL SERVICES

Technical advice, custom CAD drawings, and additional information can be obtained by contacting Stego Industries or by visiting the website.

**Contact Number:** (877) 464-7834

**Website:** [www.stegoindustries.com](http://www.stegoindustries.com)

### 10. FILING SYSTEMS

- [www.stegoindustries.com](http://www.stegoindustries.com)

(877) 464-7834 | [www.stegoindustries.com](http://www.stegoindustries.com)

DATA SHEETS ARE SUBJECT TO CHANGE. FOR MOST CURRENT VERSION, VISIT [WWW.STEGOINDUSTRIES.COM](http://WWW.STEGOINDUSTRIES.COM)

