



# STEGOCRAWL® TERM BAR

A STEGO INDUSTRIES, LLC INNOVATION | VAPOR RETARDERS 07 26 00 | VERSION: JUN 9, 2025

## 1. PRODUCT NAME

**STEGOCRAWL TERM BAR**

## 2. MANUFACTURER

Stego Industries, LLC  
216 Avenida Fabricante, Suite 101  
San Clemente, CA 92672  
Sales, Technical Assistance  
Ph: (877) 464-7834  
contact@stegoindustries.com  
stegoindustries.com



## 3. PRODUCT DESCRIPTION

**USES:** StegoCrawl Term Bar is a semi-flexible plastic termination bar used to assist in mechanically securing StegoCrawl® Wrap Vapor Barrier or other materials to concrete, masonry, foam insulation, or wood.

**COMPOSITION:** StegoCrawl Term Bar is made from post-industrial recycled PVC.

### FEATURES AND BENEFITS:

- **Bar Size:** 42" x 1.125"
- **White color** complements the white StegoCrawl encapsulation system
- **Offers a pocket/lip** to accommodate a bead of sealant or caulk
- **Pre-drilled holes** approximately every 6" facilitate easy installation
- **Easy to trim** to desired length
- **Made in the USA**



## 4. TECHNICAL DATA

**TABLE 1: PHYSICAL PROPERTIES OF STEGOCRAWL TERM BAR**

PROPERTY	RESULTS
Dimensions	42" x 1.125"; Pre-Drilled Hole Size: ¼"
Color	White
Material	Recycled PVC
Weight	4 oz (113.3 grams)

*Continued...*

Note – legal notice on page 2.

# STEGOCRAWL® TERM BAR

A STEGO INDUSTRIES, LLC INNOVATION | VAPOR RETARDERS 07 26 00 | VERSION: JUN 9, 2025

## 5. INSTALLATION

**CRAWL SPACE FOUNDATION WALL:** Install screw anchors or nails with washers (sold separately) through the pre-drilled holes that are provided approximately every 6 inches in StegoCrawl Term Bar to secure StegoCrawl Wrap Vapor Barrier or Retarder to the wall. Although we generally recommend a mechanical fastening means at every pre-drilled hole location in StegoCrawl Term Bar, appropriate spacing of screw anchors or nails can be determined by the project team. The goal is ultimately to achieve a consistent and continuous low-permeance vapor seal of the chosen sealing accessory (such as StegoTack Tape) and permanent attachment of the StegoCrawl system to the wall.

When using screw anchors, we recommend pre-drilling holes in the wall and using the holes in StegoCrawl Term Bar as the guide for drilling locations (for concrete and masonry walls, a SDS rotary hammer drill or similar is recommended for ease). Be sure to use an appropriate screw anchor for the wall composition (e.g., concrete screw for concrete wall) with a head large enough in diameter to span the 1/4" pre-drilled hole of StegoCrawl Term Bar.

If using a powder-actuated, or similar, nail gun, be sure to use appropriate nails for the wall composition, as well as nails or pins which have or can accommodate a washer. The washer will help span the 1/4" pre-drilled hole in StegoCrawl Term Bar. Please note that a powder-actuated nail gun with a higher powder load may cause StegoCrawl Term Bar to break, please use proper loads.

StegoCrawl Term Bar can be oriented so the beveled edge creates a pocket/lip to accommodate a bead of mastic, caulk, or similar sealant, as desired.

To cut StegoCrawl Term Bar, score with a utility knife or cut with wire snips. StegoCrawl Term Bar can also be bent back and forth then broken at the desired location.

StegoCrawl Term Bar is flexible enough to bend around corners and contours in the wall for easy installation.

Do not exceed 7 days between StegoCrawl Term Bar installation and concrete placement or full protection from UV and weather exposure. Please review technical data sheets for Stego accessory products for installation/application temperature range.

For more information, please refer to the complete StegoCrawl Installation Instructions.

## 6. AVAILABILITY & COST

For cost and local availability of StegoCrawl Term Bar, please contact your local Stego® Sales Representative. For online ordering, visit: [shop.stegoindustries.com](https://shop.stegoindustries.com)

## 7. WARRANTY

Stego believes to the best of its knowledge, that specifications and recommendations herein are accurate and reliable. However, since site conditions are not within its control, Stego does not guarantee results from the use of the information provided herein. Stego does offer a limited warranty on StegoCrawl Wrap. Please see [stegoindustries.com/legal](https://stegoindustries.com/legal)

## 8. MAINTENANCE AND STORAGE

**Maintenance:** None required.

**Storage and Handling:** Store above 60°F.

Please refer to the Safety Data Sheet (SDS) for detailed safety, storage, and handling procedures.

## 9. TECHNICAL SERVICES

Technical advice, custom CAD drawings, and additional information can be obtained by contacting Stego or by visiting the website.

**Email:** [contact@stegoindustries.com](mailto:contact@stegoindustries.com)

**Contact Number:** (877) 464-7834

**Website:** [stegoindustries.com](https://stegoindustries.com)

## 10. FILING SYSTEMS: [stegoindustries.com](https://stegoindustries.com)

